




# STERAMIST

ENVIRONMENT SYSTEM



| FEATURE                                 | TPO-302-02  |
|---|---|
| Voltage                                 | 110/120V AC, 5A or 220/230V AC, 5A  |
| Disinfection/Decontamination Technology | ionized Hydrogen Peroxide (iHP™)  |
| Number of iHP™ spray ports              | 3   |
| Dimensions                              | 1.2 m Length x 0.61 m Width x 0.61 m Depth (approximately 47" x 24" x 24")  |
| Weight                                  | Approximately 43.09 kg (95 lbs.) (Does not include Applicators & Stands)  |
| Particle Size                           | 0.03-3 Microns  |
| Broad Spectrum Kill                     | Yes   |
| Safe for Sensitive Equipment            | Yes   |
| Flow Rate                               | 25 ml per minute per applicator   |
| Treatment Method                        | Complete Room Disinfecting System   |
| Dose Application                        | .5 ml. per ft. <sup>3</sup>   |
| Application Rate/Time                   | Effective complete room treatment in just over 75 minutes for a room 3,663.7 ft. <sup>3</sup> /104 m <sup>3</sup>   |
| Dwell Time                              | including application time, contact time, and aeration time. Less time is typically needed for smaller size rooms. Room is safe to enter once hydrogen peroxide is below 0.2 ppm. |
| Aeration Time                           |   |
| Warranty (parts & labor)                | One (1) year (voided if seal is broken). Extended Warranty Available.   |